



ASSYST bvba / A.S.O.W. bvba  
Hellegatstraat 13a - 2590 Berlaar - Belgium  
Tel: +32 495 50 61 14 / +32 496 83 70 27  
Website: [www.assyst.org](http://www.assyst.org) / [www.artsuppliesonweb.com](http://www.artsuppliesonweb.com)  
Email: [ao@assyst.org](mailto:ao@assyst.org) / [vera.opsommer@assyst.org](mailto:vera.opsommer@assyst.org)

## GLASS FIBRE TISSUE

### **DESCRIPTION:**

Flat weave made of glass fibre and used to create more strength in a composite due to the high glass fibre to resin ratio. This woven roving is often used in combination with Chopped Strand Mats or Gun roving and is available in different weights and different fabrics such as square or twill.

These woven rovings can be used with polyester, vinyl ester and epoxy resins. Standard woven roving weights: 200, 300, 600 and 800 g/m<sup>2</sup> (all other weights available on request). The fibres used to weave that roving are usually 2400 Tex.